


Bearing type G



Bearing type K



**elesa**  
Original design RE.F8

**2 Bearing type**

- G Friction bearing
- K Ball bearing

**3 Type**

- A Wheel without bracket



d <sub>1</sub> Wheel Ø		b <sub>1</sub>		b <sub>2</sub>		d <sub>2</sub>		Recommended ergonomic max. load in N		Max. static load capacity in N		Max. dynamic load capacity in N	
Bearing type G	Bearing type K	Bearing type G	Bearing type K	Bearing type G	Bearing type K	Bearing type G	Bearing type K	Bearing type G	Bearing type K	Bearing type G	Bearing type K	Bearing type G	Bearing type K
65	-	30	-	34	-	12	-	900	-	1250	-	1200	-
80	-	30	-	39	-	12	-	1500	-	2000	-	1800	-
100	-	30	-	44	-	12	-	1750	-	3500	-	3000	-
125	125	38	45	44	56	15	20	2000	4000	4500	7000	4000	6500
150	150	45	45	58	56	20	20	2500	4550	6000	8000	5000	7500
200	200	50	50	58	56	20	20	3150	6500	8000	10000	7300	9000

**Specification**

**Wheel tread / Wheel core**

Plastic, polyamide (PA)

- Single part
- White
- Hardness 70 Shore D

**Operating temperature** -30 °C to +80 °C

RoHS

Wheels GN 22892 are used in industrial and public indoor areas for moving transport carts, for example.

The wheel tread offers low rolling resistance as well as good wear and tearing resistance.

With bearing type K, the low wear on the ball bearing increases the service life, and the mounting to the inner ring can be accomplished with zero axial backlash.

see also...

	Page
<b>GN 22892</b> Medium Duty Casters (with Bracket, Light Version)	QVX
<b>GN 22892</b> Medium Duty Casters (with Bracket, Light Version, with Leveling Foot)	QVX
<b>GN 22892</b> Medium Duty Casters (with Bracket, Medium Version)	QVX
<b>GN 22892</b> Heavy Duty Casters (with Bracket, Heavy Version)	QVX

**Technical Information**

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX

How to order

**GN 22892-80-G-A**

1	d <sub>1</sub>
2	Bearing type
3	Type

