


Rostfrei Inox Stainless Steel



- 4 Type**
- H** Vertically adjustable
 - B** Horizontally adjustable
 - HB** Vertically and horizontally adjustable
 - D** With through-holes
 - DH** With through-holes, vertically adjustable
 - DB** With through-holes, horizontally adjustable

2			3													4	
l_1	l_2	b	d_1	d_2	h_1	h_2	h_3	h_4	l_3	l_4	m_1	m_2					
D, DH, H	DB, HB, B								D, DH, H	DB, HB, B	D, DH, H, DB, HB, B						
40	45	50	45	5,3	5,3	4	13	5	9,5	19	16	21	16	21	25	25	
50	55	60	55	6,5	6,5	6	16,6	6	11,6	23,2	21	26	21	26	30	30	
60	68	76	65	8,3	8,3	8	21,4	8	14,9	29,8	26	33,5	26	33,5	36	36	

Specification

- Zinc die casting **ZD**
- Powder coated
- Black, RAL 9005, textured finish **● SW**
- Silver, RAL 9006, textured finish **● SR**
- Stainless steel AISI CF-8 **NI**
- Matte shot-blasted **GS**
- Pin
- Stainless steel AISI 316Ti
- Load Rating Information → Page 2121
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- SST Spacer Plates GN 2370 → Page 1350
- SST Plates with Tapped Holes GN 2372 → Page 1351

Information

Hinges GN 235 are adjustable in height or width along the slots, depending on the design, and are fastened with hex-head, oval-head or cylinder screws with a low head.

Thanks to sufficient space (installation space) available for screw heads and washers, the hinges can be opened by 180° without collision.

The hinge drill pattern corresponds with that of the GN 237 hinge family, which allows the hinges to be exchangeable.

see also...

- List of Hinge Types → Page 1284 ff.
- Hinges GN 237 → Page 1292

How to order

1	Material
2	l_1
3	l_2
4	Type
5	Finish

GN 235-ZD-45-45-DB-SR