




3 Form
BJ Adjustable on both sides
EJ One-sided adjustable
NJ Not adjustable



1 l_1	2 l_2	d_1	d_2	$h_1 \approx$	$h_2 \approx$	h_3	l_3	m_1	m_2
42	42	5,3	4	11	6,5	7,5	17	25	25
50	50	6,3	5	13,5	7	8,5	21	30	30
60	60	6,3	6	16,5	8,5	11	26	36	36

Specification

- Hinge leaves**
Zinc die casting
Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Silver, RAL 9006, textured finish **● SR**
- Adjusting disks**
Stainless steel AISI 303
- Covers**
Plastic
 - Black gray for type SW
 - Light gray for type SR
- Pin**
Stainless steel AISI 303
- RoHS

The adjustable hinges GN 238 allow the technically and visually perfect positioning and alignment of a door in its frame. The steel adjusting disc has a cutting ring in its underside which cuts into the radial fins of the zinc die-cast leaf when the countersunk screw is tightened, virtually creating a form-lock that prevents adjusting the hinge after mounting. The covers conceal the fixing elements and lend the hinge an attractive optical appearance.

see also...
GN 127 Hinges (Zinc Die Casting / Stainless Steel, Adjustable) QVX
GN 236 Hinge (Plastic, Adjustable) QVX

Technical Information	Page
Swiveling Range / Assembly Instruction	QVX
Overview of Latch Types	QVX
Load rating information of metal hinges	QVX
Stainless Steel Characteristics	QVX


How to order

1	l_1
2	l_2
3	Type
4	Color


GN 238-50-50-BJ-SW



Swivelling Range



Function (Type BJ)



Assembly Instruction

