



elesa
Original design
RE.F8-N / RE.F8-SST-N



- 2 Bearing type**
- G Friction bearing
- 3 Type (bracket)**
- B Rigid bracket
- L Swivel bracket with mounting plate
- LF Swivel bracket with mounting plate, with total lock brake
- R Swivel bracket with center hole
- RF Swivel bracket with center hole, with total lock brake
- 4 Coding**
- L Light version

d ₁ Wheel Ø	b	d ₂	d ₃	d ₄	h	l ₁		l ₂		l ₃	m ₁		m ₂		m ₃	m ₄	r	Max. dynamic load capacity in N
						Type B / L / R	Type LF / RF	Type B	Type L / LF		Type B	Type L / LF						
65*	-	30	9	12	73	100	100	100	85	85	40	45	60	60	75	80	-	1200
80	80	30	9	12	73	107	107	100	85	85	40	45	60	60	75	80	120	1800
100	100	30	9	12	73	128	128	100	85	85	35	45	60	60	75	80	120	2000
125	125	38	9	12	73	156	156	100	85	85	37	45	60	60	75	80	120	2200
150	150	45	11	20	102	194	188	140	114	110	56	73	85	87	105	105	156	3000
200	200	50	11	20	102	240	236	140	114	110	56	73	85	87	105	105	156	3000

* Only available in version ST

Specification

Wheel tread / Wheel core

- Plastic, polyamide (PA)
- Single part
- White
- Hardness 70 Shore D

Bracket

- Steel sheet metal, zinc plated **ST**
- Stainless steel sheet metal AISI 304 **NI**

Swivel head bracket

- Dual grease-lubricated ball bearing
- Dust protection ring on type L / LF
- Plastic, polyethylene (PE)

Operating temperature -30 °C to +80 °C

RoHS

Technical Information

Operating Conditions of Wheels and Casters QVX
 Technical Information for Wheels and Casters QVX

Medium duty casters GN 22892 are used in industrial and public indoor areas for moving lightweight carts, for example.

The wheel tread offers low rolling resistance as well as good wear and tearing resistance.

see also...

	Page
GN 22892 Wheels (without Bracket)	QVX
GN 22892 Medium Duty Casters (Light Version, with Leveling Foot)	QVX
GN 22892 Medium Duty Casters (Medium Version)	QVX
GN 22892 Heavy Duty Casters (Heavy Version)	QVX

How to order

1	d ₁
2	Bearing type
3	Type (bracket)
4	Coding
5	Material (bracket)

GN 22892-80-G-RF-L-NI