


- 3 Type**
- BJ** Adjustable on both sides
 - EJ** One-sided adjustable
 - NJ** Not adjustable



1 **2**

l_1	l_2	d_1	d_2	$h_{1\approx}$	$h_{2\approx}$	h_3	l_3	m_1	m_2
42	42	5,3	4	11	6,5	7,5	17	25	25
50	50	6,3	5	13,5	7	8,5	21	30	30
60	60	6,3	6	16,5	8,5	11	26	36	36

Specification

- Zinc die casting
Powder coated
Black, RAL 9005, textured finish
Silver, RAL 9006, textured finish
- Adjusting disk
Steel, hardened
- Cover
Plastic
- Black gray for type SW
- Light gray for type SR
- Pin
Stainless Steel AISI 303
- Load Rating Information → Page 2121
- Stainless Steel Characteristics → Page 2166
- RoHS

- SW
- SR

4

Information

The adjustable hinges GN 238 allow the technically and visually perfect positioning and alignment of doors in their frames.

The steel adjusting disc has a cutting ring in its underside which cuts into the radial fins of the zinc die-cast leaf when the countersunk screw is tightened, virtually creating a form-lock that prevents adjusting the hinge after mounting.

The covers conceal the fixing elements and lend the hinge an attractive optical appearance.

see also...

- List of Hinge Types → Page 1284 ff.
- Hinges GN 127 (Adjustable, Zinc Die Casting) → Page 1375
- Hinge GN 236 (Adjustable, Plastic) → Page 1376

How to order

GN 238-50-50-BJ-SW

1	l_1
2	l_2
3	Type
4	Color



3.1


3.2

3.3


3.4

3.5

Swiveling range




Function (Type BJ)



3.6

3.7

Assembly instruction



3.8

3.9

