



**elesa**  
Original design RE.F8-H

- 2 Bearing type**  
G Friction bearing
- 3 Type (bracket)**  
B Rigid bracket  
L Swivel bracket with mounting plate  
LF Swivel bracket with mounting plate, with total lock brake
- 4 Coding**  
M Medium version

**1**

d <sub>1</sub> Wheel Ø	b	d <sub>2</sub>	h	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	m <sub>1</sub>	m <sub>2</sub> Type B Type L / LF	m <sub>3</sub>	m <sub>4</sub>	r	Max. dynamic load capacity in N	
100	38	9	138	100	85	46	45	60	60	75	80	123	3500
125	50	11	170	140	115	70	73	85	87	105	105	126	5500
150	50	11	200	140	115	70	73	85	87	105	105	126	7000
200	50	11	250	140	115	70	73	85	87	105	105	126	7500

**Specification**

**Wheel tread / Wheel core**

- Plastic, polyamide (PA)
- Single part
- White
- Hardness 70 Shore D

**Bracket**

Steel sheet metal, zinc plated

**ST**

**Swivel head bracket**

- Dual grease-lubricated ball bearing
- Dust protection ring on type L / LF
- Plastic, polyethylene (PE)

**Operating temperature** -30 °C to +80 °C

RoHS

**5**

Medium duty casters GN 22892 are used in industrial and public indoor areas for moving medium weight carts, for example. The wheel tread offers low rolling resistance as well as good wear and tearing resistance.

see also...

	Page
GN 22892 Wheels (without Bracket)	QVX
GN 22892 Medium Duty Casters (Light Version)	QVX
GN 22892 Medium Duty Casters (Light Version, with Leveling Foot)	QVX
GN 22892 Heavy Duty Casters (Heavy Version)	QVX

**Technical Information**

Operating Conditions of Wheels and Casters QVX

Technical Information for Wheels and Casters QVX

How to order

<b>1</b>	d <sub>1</sub>
<b>2</b>	Bearing type
<b>3</b>	Type (bracket)
<b>4</b>	Coding
<b>5</b>	Material (bracket)

**GN 22892-200-G-L-M-ST**

