



2 Type

- N** Normal roller carriage, central arrangement
- R** Radial roller carriage, lateral arrangement
- S** Narrow roller carriage, central arrangement

3 Version

- U** With wiper for floating bearing rail (U-rail)
- X** With wiper for fixed bearing rail (X-rail)

1

Type N										
h ₁ Rail	b ₁	b ₂	b ₃	d ₁	d ₂	h ₂	l ₁	l ₂	m	A/F
18	8,3	16,5	7,2	14	M 5	17	76	62	52	8
28	12,3	24,1	10	22,4	M 5	25	116	102	78	13
43	21	37,5	15	35	M 8	40	148	134	114	15

Type S / Type R																			
h ₁ Rail	b ₁	b ₂		b ₃		d ₁	d ₂		d ₃	h ₂		h ₃	l ₁	l ₂	m		s	t	A/F
		Type S	Type R	Type S	Type R		Type S	Type R		Type S	Type R				Type S	Type R			
18	8,3	15	17,3	5,7	8	14	M 5	M 5	M 4	9,5	20	4	74	60	20	20	17	8	8
28	12,3	23,8	24,1	9,7	10	22,4	M 5	M 6	M 5	15	30	4	94	80	35	36	24,5	10	13
35	16,5	30	30	12	12	28	M 6	M 8	M 6	20	36	3	114	100	45	45	29,5	15	15
43	21	37	37,5	14,5	15	35	M 8	M 8	M 6	25	45	4	134	120	55	56	38,5	16	15

Specification

- Base body
 - Aluminum (Type N / Type R)
 - Steel (Type S)
 - Zinc plated, blue passivated
- Rollers
 - Anti-friction bearing steel, hardened
 - Ball mounted, sealed (2RS)
 - Permanent lubrication
- Wiper
 - Plastic, PUR, gray
 - Steel insert, zinc plated
- RoHS

On request

- Cam roller carriages with more than 3 rollers
- Other roller arrangements

Information

Cam roller carriages GN 2424 are combined with cam roller linear guide rails GN 2422 to build linear guide rail systems. They are used in mechanical engineering or jigmaking for the linear movement of plant equipment.

Depending on cam roller carriage type, these can be mounted in axial or radial direction to the roller axes. Also depending on rail type, matching wipers are mounted, with type N featuring additional sealing lips in longitudinal direction.

see also...

- [Structure Linear Guide Rail Systems](#) → Page 1918
- [Cam Roller Linear Guide Rails GN 2422](#) → Page 1921
- [Cam Rollers GN 2426](#) → Page 1924
- [Linear Guide Rail Systems \(Technical Information etc.\)](#) → Page 1926 ff.

How to order

GN 2424-35-N-X

1	h ₁
2	Type
3	Version