

elesa
Original design RE.F7-HT


2 Bearing type

- B** Bore
- G** Friction bearing

3 Type

- A** Wheel without bracket

Assembly instruction



1 d ₁ Wheel Ø	b ₁	b ₂	d ₂	d ₃	l ₁	l ₂	s	A/F	Recommended ergonomic max. load in N	Max. static load capacity in N	Max. dynamic load capacity in N
80	35	39	12	M 8	55	5,5	2,5	13	1250	2500	1500
100	35	44	12	M 8	60	5,5	2,5	13	1300	3000	2000

Specification

Wheel tread / Wheel core

- Plastic, Phenolic (PF)
- Single part
- Black
- Hardness 90 Shore D

Bearing type G

- Friction bearing
- Plastic, polytetrafluoroethylene (PTFE)
- Screws / Nuts
- Steel
- Axis
- Stainless steel

Operating temperature -20 °C to +300 °C

RoHS

Wheels GN 22894 are used in industrial and public indoor areas for moving transport carts, for example. They are characterized by their high operating temperature.

see also...

	Page
GN 22894 Medium Duty Casters (with Bracket, Light Version)	QVX

Technical Information

Overview of Types of Wheels	QVX
Operating Conditions for Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX

How to order

GN 22894-80-G-A

- 1** d₁
- 2** Bearing type
- 3** Type