



Length l	¹ d ₁ H9 Bore	² s H11 Square	d ₂	h ₁	h ₂ ≈	h ₃	h ₄ ≈	Ø Handle
80	B 10	V 10	22	22	15,4	6,6	45	18
100	B 12	V 12	26	26	17,7	8,3	55	21
125	B 14	V 14	28	28	18,8	9,2	71	23
160	B 17	V 17	32	32	22,6	9,4	71	23
200	B 19	V 19	38	38	28	9,4	71	23

Specification

Body

Stainless steel precision casting AISI CF-8
Contact face of hub machined

Revolving handle similar to GN 598.1

Plastic, phenolic resin (PF)

- Black, shiny finish
- Spindle
- Stainless steel AISI 304

RoHS

On request

- with retractable handle GN 798.5

Cranked handles GN 269 have been designed to comply with stringent hygiene requirements.

The cylindrical handles are made of phenolic resin material which in general provides good stability when exposed to chemicals.

Technical Information

	Page
Cross holes GN 110	QVX
Squares DIN 79	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 269-100-V12

¹ Length l

² d₁ (s)

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

