

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

Mounting information	
<p>Hinge, left</p> <p>Hinge, right</p>	<p>Left / right hinges</p> <p>Right or left hinges can be created by the direction in which the bearing bushings are inserted into the hinge wing.</p>
<p>Door to be unhinged</p> <p>Door not to be unhinged</p> <p>Cabinet U-handle GN 565.1</p>	<p>Mounting on door frames</p> <p>For mounting a door that should be removable, two hinges of the same type must be attached to the door frame.</p> <p>If the door is not supposed to be removable, the door must be mounted with at least one right hinge and at least one left hinge.</p>
<p>M6x20</p> <p>1.</p> <p>2.</p> <p>3.</p> <p>4.</p> <p>5.</p> <p>6.</p> <p>7.</p>	<p>Mounting</p> <ol style="list-style-type: none"> 1. Position the bearing bushing with the desired installation direction on the hinge wing. Then insert a screw with a collar such as socket button head screws ISO 7380 into the bearing bushing to protect the bearing bushing collar from damage while pounding in. 2. Pound in the bearing bushing until about 1 mm remains between the bearing bushing collar and the hinge wing. 3. Remove the burr on the bearing bushing using a knife. 4. Pound in the bearing bushing all the way. 5. Remove the screw. 6. Pound a tapered dowel pin into the bearing bushing. 7. Place the cover cap on the opposite side of the hinge wing. <p>Insert the other bearing bushings according to points 1 to 5.</p>