


Type A




3 Type


- A Exterior hinge leafs
- I Interior hinge leafs

4 Identification no.


- C With countersunk holes




Type I



Assembly instruction



Type A



Type I

1		2											
l_1		l_2	d_1	d_2	l_3	l_4	l_5	m_1		m_2	m_3	m_4	s
Type A	Type I							Type A	Type I				
72	86	82	6,6	14	40	36	43	40,8	55	42	-	-	3,5
72	86	162	6,6	14	80	36	43	40,8	55	-	50	32	3,5

Specification

- Aluminum Anodized, natural color **EL**
- Bearing bushing / cover cap
 - Plastic Technopolymer (Polyamide PA)
 - Graphite gray, RAL 7024
- Tapered dowel pin ISO 8741 Steel zinc plated, blue passivated
- Plastic Characteristics → Page 2158
- RoHS

On request

- Other lengths and hole spacings
- Other finishes

5

Information

Hinges GN 2294 are made of drawn profiled aluminum and are used on doors and covers, for example.

Given the external hinge leaf, type A hinges allow mounting with a very small door gap. The type I is fastened in the door gap. The mounting screws are therefore inaccessible and hence protected from vandalism when the door is closed.

The hinges are delivered loose and must be mounted according to the accompanying instructions. Any hinge combination may be realized thanks to the modular design and available accessories.

How to order

1	l_1
2	l_2
3	Type
4	Identification no.
5	Finish

GN 2294-86-162-A-C-EL

