


Type OZ

Type AV



elesa


Original design TCC-PB / TCC-PBF



3 Type

OZ Without centring step (smooth)

AV With external serration



1

2

b	x <sub>1</sub>	d <sub>1</sub>	d <sub>2</sub>	Length l	m <sub>1</sub>	m <sub>2</sub>	t <sub>1</sub>	t <sub>2</sub>	s	x <sub>2</sub>	y <sub>1</sub>	y <sub>2</sub>
40	40	8,5	6,5	54	33	20	-	8	13,5	-	75	60
40	75	8,5	6,5	54	33	37,5	30	8	13,5	60	75	60

Specification

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature -20 °C to +100 °C
- Black, RAL 9005, matte finish
- Gray, RAL 7040, matt finish

- SW
- GR

RoHS

The fixing lug of the swivel clamp connectors GN 272.9 is available with a smooth surface or with external serration.

The flange with two or four bores serves for fastening the clamp connector. Swivel clamp connectors GN 272.9 can be assembled with swivel clamp connectors GN 276.9 and GN 278.9 to create swivel clamp connector joints.

see also...

	Page
GN 282.9 Swivel Clamp Connector Joints	QVX
GN 276.9 Swivel Clamp Connectors	QVX
GN 278.9 Swivel Clamp Connectors	QVX
GN 272 Swivel Clamp Connectors (Aluminum)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order

1	b
2	x <sub>1</sub>
3	Type
4	Color

GN 272.9-40-75-OZ-SW