


3 Type


- A Exterior hinge leaves
- I Interior hinge leaves

4 Coding

- C With countersunk holes



Assembly instruction



1		2		5										
l_1		l_2	d_1	d_2	l_3	l_4	l_5	l_6	m_1		m_2	m_3	m_4	s
Type A	Type I								Type A	Type I				
72	86	245	6,6	14	80	80	36	43	40,8	55	50	32,5	50	3,5
72	86	415	6,6	14	80	250	36	43	40,8	55	50	67,5	150	3,5
72	86	565	6,6	14	80	400	36	43	40,8	55	50	67,5	150	3,5

Specification

Hinge leaves

Aluminum
Anodized, natural color ● EL

Bearing bushing / Cover cap

Plastic, Polyamide (PA)
Graphite gray, RAL 7024

Tapered dowel pin ISO 8741

Steel
Zinc plated, blue passivated

RoHS

On request

- Other lengths and hole spacings
- Other finishes

Technical Information

	Page
Mounting information	QVX
List of Hinge Types	QVX
Plastic Characteristics	QVX

Hinges GN 2295 are made of drawn profiled aluminum and are used on doors and covers, for example.

Given the external hinge leaves, type A hinges allow mounting with a very small door gap. The type I is fastened in the door gap. The mounting screws are therefore inaccessible and hence protected from vandalism when the door is closed.

The hinges are delivered loose and must be mounted according to the accompanying instructions. Any hinge combination may be realized (if needed, also by shortening the middle wing) thanks to the modular design and available accessories.

see also...

GN 2295 Hinges

Page

QVX

How to order

1	l_1
2	l_2
3	Type
4	Coding
5	Finish

GN 2295-86-565- I -C-EL