




Application example



2

3

$l_2$	$w \approx$ Angle of rotation in °	b	d	h	$l_1$	$m_1$	$m_2$	s
40	150	12	5,3	7,8	40	25	25	3,5
50	150	15	6,3	9,2	50	30	30	4
60	150	18	8,3	10,9	60	36	36	5

**Specification**

1

4

- Steel precision casting **ST**
- Zinc plated, powder coated
- Black, RAL 9005, textured finish **SW**
- Elastomer element
  - NBR (Perbunan®)
  - Temperature resistant up to 120 °C
  - Hardness 85±5 Shore A
- *Plastic Characteristics* → Page 2158
- **RoHS**

**Information**

In terms of their dimensions, rubber bumper stops GN 2374 have been designed as extras for the GN 237 and GN 337 family of hinges. They can also be bolt-attached when mounting the hinge, with an elastomer element limiting the angle of rotation to the value w.

They are mainly used for lighter traps and gates, or when the limit stop is not expected to be exposed to dynamic loads.

see also...

- *Hinges GN 237* → Page 1292
- *Hinges GN 237.1 (Plastic)* → Page 1296
- *Hinges GN 337 (Detachable)* → Page 1378
- *Hinges GN 337.1 (Detachable)* → Page 1379

How to order

**GN 2374-ST-40-150-SW**

- 1 Material
- 2  $l_2$
- 3 w
- 4 Finish