



**Rost** frei  
Inox  
Stainless  
Steel

**4 Type**

- A 2x2 bores for countersunk screws
- C 2x2 threaded studs

**2**

**3**

$l_1$		$l_2$	$d_1$	$d_2$	$d_3$	$h_1$	$h_2$	$h_3$	$h_4 + 0,5$	$l_3$		$l_4$		$l_5$	$m_1$	$m_2$	$m_3$	$m_4$
Elongated on one side	Elongated on both sides									ZD	NI	ZD	NI					
63	-	50	M 6	6,3	6	11,5	6	6,5	13	18,5	21	31,5	34	12	43	30	15	28
-	76	50	M 6	6,3	6	11,5	6	6,5	13	31,5	34	31,5	34	12	56	30	28	28
90	-	60	M 8	8,4	8	15	8	8,5	17	21,5	26	51,5	56	14	63	36	18	45
-	120	60	M 8	8,4	8	15	8	8,5	17	51,5	56	51,5	56	14	90	36	45	45

**Specification**

**1**

**5**

- Zinc die casting **ZD**  
Powder coated  
Black, RAL 9005, textured finish ● **SW**  
Silver, RAL 9006, textured finish ● **SR**
- Stainless steel AISI CF-8 **NI**  
(only type A)  
Matte shot blasted **GS**
- Pin  
- Stainless steel AISI 303 for ZD  
- Stainless steel AISI 316L for NI
- Threaded stud (type C)  
Stainless steel AISI 316
- *Load Rating Information* → Page 2121
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

Hinges GN 237 with horizontally elongated hinge wings are made in a compact and sturdy design. They are used when larger spacings are required for the attachment bore holes.

**see also**

- *List of Hinge Types* → Page 1284 ff.
- *Plates with Tapped Holes GN 2372 (Stainless Steel)* → Page 1351
- *Spacer Plates GN 2370 (Stainless Steel)* → Page 1350
- *Rubber Bumper Stops GN 2374* → Page 1298

**How to order**

<b>1</b> Material
<b>2</b> $l_1$
<b>3</b> $l_2$
<b>4</b> Type
<b>5</b> Finish

**GN 237-ZD-76-50-A-SR**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9