




STAIN
LESS

4 Type

- A 2x3 bores
for countersunk screws
- C 2x3 threaded studs

l ₁	l ₂	d ₁	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ +0,5	l ₃	l ₄ ZD	NI	m ₁	m ₂	m ₃
30	45	M 4	4,3	3	7,5	4	4,3	8,6	11	9	9	18	33	16,5
40	60	M 5	5,3	4	9	5	5,5	11	16	12	11	25	45	22,5
50	75	M 6	6,4	6	11,5	6	6,5	13	21	12	13	30	55	27,5
60	90	M 8	8,4	8	15	8	8,5	17	26	14	17	36	66	33
80	120	M 10	10,5	10	20	10	10,5	21	36	18	21	50	90	45

Specification

Hinge leafs

- Zinc die casting
- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish
- Stainless steel AISI CF-8
- Matte shot-blasted finish

ZD

- SW
- SR

NI

GS

Pin

- Stainless steel AISI 303 for ZD
- Stainless steel AISI 316Ti for NI
- For l₁ = 50 / 60 / 80 lubricated

Threaded studs for type C

- Stainless steel AISI 304 for ZD
- Stainless steel AISI CF-8 for NI
- casted „in one piece“

RoHS

Hinges GN 237 with vertically elongated hinge leafs are made in a compact and sturdy design and require little space on the sides. They are used when a greater load capacity and better transmission of force to the surrounding structure is required.

Type C hinges with threaded studs are shrouded and fastened from the rear side to prevent vandalism.

see also...

	Page
GN 237 Hinges (Square)	QVX
GN 237 Hinges (Horizontally Elongated)	QVX
GN 337 Hinges (Detachable)	QVX
GN 235 Hinges (Adjustable)	QVX
GN 238 Hinges (Adjustable)	QVX
GN 237.1 Hinges (Plastic)	QVX

Technical Information

List of Hinge Types	QVX
Load rating information of metal hinges	QVX
Stainless Steel Characteristics	QVX

How to order

1	Material
2	l ₁
3	l ₂
4	Type
5	Finish

GN 237-ZD-50-75-C-SW