




Ø2^{H12} x 4
Hole for pin
for swivel limiting stop



Bore for
socket cap screw
DIN 912-M4

Application example



Side thrust pin
GN 614.1

3.1

3.2

3.3

3.4

3.5



h	b ±0,1	for GN 614				for GN 615 / GN 615.2 / GN 615.3			
		Size	d	w	s min.	Size	d	w	s min.
8,5	3,4	6	5	1,6	0,9	M 8	4,5	1,5	0,8
10,5	4,5	8	6,5	1,9	1	M 10	6	2	1

3.6

Specification

- Sintered steel
 - Case-hardened
 - Plain
- RoHS

Information

Indent blocks GN 250 are used together with spring plungers for detent or positioning of sliders, flaps and similar applications.

see also...

- *Spring Plungers GN 614* → Page 982
- *Spring Plungers GN 615* → Page 976
- *Plastic Spring Plungers GN 615.2* → Page 978
- *Spring Plungers GN 615.3* → Page 977
- *Side Thrust Pins GN 614.1* → Page 1001

3.7

3.8

3.9

How to order	1	h
GN 250-8,5		

