



1 l_1	2 d_1 Thread			2 d_2 H7 Bore		d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
22	M 3	M 4	M 5	-	-	8	10,5	18,5	2	23	3	5
30	M 3	-	-	-	-	10	13	24,5	4	31	3,5	7
30	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	31	3,5	8
45	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	34	3,5	8
63	M 6	M 8	-	B 8	-	13,5	17,5	31	6,5	45	4	11
78	M 8	M 10	M 12	B 8	B 10	16	21	36	8	54	4	14
92	M 10	M 12	-	B 12	-	19	24	43	11	64	4	17
108	M 12	M 16	-	B 12	B 16	23	30	50,5	12	75	5	22

Specification

- Handle
Zinc die casting
- Powder coated
Black, RAL 9005, textured finish **● SW**
Black, RAL 9005, silk finish **● SZ**
Orange, RAL 2004, textured finish **● OS**
Red, RAL 3000, textured finish **● RS**
Silver, RAL 9006, textured finish **● SR**
- Chrome plated **● CR**
- Uncoated **● RH**
Tumbled
- Bushing and retaining screw
Stainless steel AISI 303
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

On request

- With inch threads

Information

Adjustable hand levers GN 300.1 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- Adjustable Hand Levers GN 300 (Bushing Steel) → Page 428
- Adjustable Hand Levers GN 300.5 (Stainless Steel, Matte Shot-Blasted) → Page 440
- Adjustable Hand Levers GN 300.6 (Stainless Steel, Polished) → Page 440
- Adjustable Hand Levers GN 303.1 (with Push Button) → Page 446

How to order

GN 300.1-78-M10-OS

1	l_1
2	d_1
3	Color (Finish)