



1

2

| l_1 | d_1 | d_3 | d_4 | h_1 | h_3 | h_4 Stroke | t min. |
|-------|-------|-------|-------|-------|-------|-----------------|-------------|
| 63 | M 6 | 24 | 17,5 | 34,5 | 48,5 | 4 | 12,5 |
| 78 | M 8 | 25 | 21 | 39,5 | 58,5 | 4 | 14 |
| 92 | M 10 | 30 | 24 | 46,5 | 68,5 | 4 | 18 |
| 108 | M 12 | 35 | 30 | 56,5 | 82 | 5 | 26,5 |

Specification

3

- Handle
Zinc die casting
- Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Black, RAL 9005, silk finish ● **SZ**
 - Orange, RAL 2004, textured finish ● **OS**
 - Red, RAL 3000, textured finish ● **RS**
 - Silver, RAL 9006, textured finish ● **SR**
- Chrome plated ● **CR**
- Bushing
Steel
Nitrided, blackened
- Retaining screw
Steel, blackened
- RoHS

Information

Adjustable hand levers GN 300.4 are produced with a clamping area which is linked via a thrust ball bearing (axial bearing) to the threaded bushing of the hand lever. This has led to the following advantages:

- **Doubled** clamping force through vastly reduced friction.
- There is no movement on the contact area between adjustable hand lever and component which greatly reduces any marking on the clamping area.
- In addition a reduced creep factor has been achieved by the increased preload.

How to order

GN 300.4-78-M8-SW

| | |
|---|----------------|
| 1 | l_1 |
| 2 | d_1 |
| 3 | Color (Finish) |