


**4 Type**

**AS** With external hex

**IS** With internal hexalobular



1		2		3														
$l_1$	$d_1$	$l_2$		$d_3$	$d_4$	$h_1$	$h_2$	$h_3$	$h_4$	Stroke								
30	M 3	-	-	6	8	10	12	16	-	-	10	13	24,5	4	31	3,5		
30	M 4	-	-	12	16	20	25	32	-	-	10	13	24,5	4	31	3,5		
30	M 5	M 6	-	12	16	20	25	32	40	50	10	13	24,5	4	31	3,5		
45	M 4	-	-	12	16	20	25	32	-	-	10	13	24,5	4	34	3,5		
45	M 5	M 6	-	12	16	20	25	32	40	50	10	13	24,5	4	34	3,5		
63	M 6	M 8	-	16	20	25	32	40	50	63	13,5	17,5	31	6,5	45	4		
78	M 8	M 10	M 12	20	25	32	40	50	63	80	16	21	36	8	54	4		
92	M 10	M 12	-	20	25	32	40	50	63	80	19	24	43	11	64	4		

**Specification**

- GN 300.5**  
Handle  
Stainless steel precision casting AISI CF-8  
Matte shot-blasted
- GN 300.6**  
Handle  
Stainless steel precision casting AISI CF-8  
Polished
- Threaded stud  
Stainless steel AISI 303
- Retaining screw  
Stainless steel AISI 303
- Pressure spring  
Stainless steel AISI 301
- Stainless Steel Characteristics → Page 2166
- RoHS

**On request**

- With inch threads

**Information**

Adjustable hand levers GN 300.5 / GN 300.6 with solid stainless steel handle, correspond to applications where „aggressive“ surrounding conditions are given, or where stainless steel materials are prescribed such as in food processing or chemical industry.

Retaining screws with hex head (Type AS) comply with the requirement „prevents water from accumulating“.

Adjustable hand levers have proved to be ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

How to order (Matte shot-blasted)

**GN 300.5-63-M8-32-IS**

1	$l_1$
2	$d_1$
3	$l_2$
4	Type

How to order (Polished)

**GN 300.6-92-M12-50-AS**

1	$l_1$
2	$d_1$
3	$l_2$
4	Type