



1 2 3

1		2		3								d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	
l ₁	d ₁			l ₂														
22	M 3	-		6	8	10	12	16	-	-	-	8	10,5	18,5	2	23	3	
22	M 4	M 5		12	16	20	25	32	-	-	-	8	10,5	18,5	2	23	3	
30	M 3	-		6	8	10	12	16	-	-	-	10	13	24,5	4	31	3,5	
30	M 4	-		12	16	20	25	32	-	-	-	10	13	24,5	4	31	3,5	
30	M 5	M 6		12	16	20	25	32	40	50	-	10	13	24,5	4	31	3,5	
45	M 4	-		12	16	20	25	32	-	-	-	10	13	24,5	4	34	3,5	
45	M 5	M 6		12	16	20	25	32	40	50	-	10	13	24,5	4	34	3,5	
63	M 6	M 8		12	16	20	25	32	40	50	63	13,5	17,5	31	6,5	45	4	
63	M 10	-		20	25	32	40	50	63	80	-	13,5	17,5	31	6,5	45	4	
78	M 8	M 10		16	20	25	32	40	50	63	80	16	21	36	8	54	4	
78	M 12	-		20	25	32	40	50	63	80	-	16	21	36	8	54	4	
92	M 10	M 12		16	20	25	32	40	50	63	80	19	24	43	11	64	4	
92	M 16	-		25	32	40	50	63	80	-	-	19	24	43	11	64	4	
108	M 12	M 16		25	32	40	50	63	80	120	-	23	30	50,5	12	75	5	

Specification

- Handle
Zinc die casting
- Powder coated
Black, RAL 9005, textured finish ● **SW**
Black, RAL 9011, silk finish ● **SZ**
Orange, RAL 2004, textured finish ● **OS**
Red, RAL 3000, textured finish ● **RS**
Silver, RAL 9006, textured finish ● **SR**
- Chrome plated ● **CR**
- Uncoated ● **RH**
Tumbled
- Threaded stud and retaining screw
Steel
- Property class 5.8
- Blackened
- Strength Values of Screws → Page 2152
- RoHS
- On request
- With inch threads

Information

Adjustable hand levers GN 300 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- Adjustable Hand Levers GN 300.1 (Threaded Stud Stainless Steel) → Page 439
- Adjustable Stainless Steel Hand Levers GN 300.5 → Page 441
- Flat Adjustable Hand Levers GN 302 → Page 449
- Adjustable Hand Levers GN 300.4 (Increased Clamping Force) → Page 435

How to order

GN 300-63-M8-25-SW

1	l ₁
2	d ₁
3	l ₂
4	Color (Finish)