



- 3 Identification no.**
- 2** With stainless steel socket cap screw DIN 912

1 **2**

d ₁ Bore for clamping Ø	d ₂ Bore for sensor	b Swivel width	d ₃	k	l ₁	l ₂	m	t	z Screw location	Accessory Recom. hand lever GN 911 for z l ₃		
B 12	B 12	B 18	25	27	31,5	64	34,5	29,5	11	M6-20	63	-
B 14	B 12	B 18	25	27	31,5	64	34,5	29,5	11	M6-20	45	63
B 15	B 12	B 18	25	27	31,5	64	34,5	29,5	11	M6-20	45	63
B 16	B 12	B 18	25	27	31,5	64	34,5	29,5	11	M6-20	45	63
B 18	B 12	B 18	25	27	31,5	64	34,5	29,5	11	M6-20	45	63

Specification

- Aluminum
Powder coated
Black, RAL 9005, textured finish **● SW**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Accessory

- Adjustable Hand Levers GN 911
→ Page 1784

4

Information

The clamping bore of sensor holders GN 275.4 is mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw location z, the socket cap screw reduces the bore cross-section for clamping.

For clamping without tools, the socket cap screw can be replaced by an adjustable hand lever GN 911 listed in the table as accessory.

see also...

- *Construction Tubes GN 990* → Page 1835
- *Retaining Rods / Tubes GN 480.1* → Page 1833
- *Universal Work Holdings GN 177 (for Work Gripper Blocks GN 177.1)*
→ Page 1806
- *Attachment Mounting Clamps GN 478* → Page 1795

How to order

1	d ₁
2	d ₂
3	Identification no.
4	Finish

GN 275.4-B16-B18-2-SW