



- 2 Type**
OZ Without centring step
- 3 Identification no.**
2 With 2 stainless steel socket cap screws DIN 912

d ₁ Bore	s ₁ Square	b Swivel width	d ₂	k Clamping length	l ₁	l ₂	m	s ₂	t	z Screw locations	Accessory Recom. hand lever GN 911 for z l ₃	
B 40	V 40	65	10,5	76	166,5	70	85	17	35	M10-60	78	92
B 42	-	65	10,5	76	166,5	70	85	17	35	M10-60	78	92
B 45	V 45	65	10,5	76	166,5	70	85	17	35	M10-60	78	92
B 48	-	65	10,5	76	166,5	70	85	17	35	M10-60	78	92
B 50	V 50	65	10,5	76	166,5	70	85	17	35	M10-60	78	92

Specification

- Aluminum
 - Powder coated
Black, RAL 9005, textured finish ● **SW**
 - Plain, matte shot-blasted ○ **BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

Information

The clamping bore of swivel clamp connectors GN 279 is not machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

The versions with square bores are also suitable for **profile systems**.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

Two swivel clamp connectors GN 279 can be combined to swivel clamp connector joints GN 289.

Swivel clamp connectors GN 279 can be combined with swivel clamp connectors GN 272, GN 274 or GN 276 to swivel clamp connector joints.

see also...

- *Construction Tubes GN 990* → Page 1835
- *Swivel Clamp Connector Joints GN 289 (Split Assembly)* → Page 1773

<p>How to order</p> <p>GN 279-V40-OZ-2-BL</p>	1	s ₁ (d ₁)
	2	Type
	3	Identification no.
	4	Finish

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

