




d ₁ Bore	b Swivel width	d ₂	k	l ₁	l ₂	m ₁	m ₂	t	x ₁	x ₂	y	z ₁ / z ₂ Screw locations	Accessory			
													Recommended hand lever			
													GN 911 for aluminum	GN 911.3 for stainless steel	GN 911 for aluminum	GN 911.3 for stainless steel
													for z ₁ l ₃	for z ₂ l ₃	for z ₁ l ₃	for z ₂ l ₃
B 12	25	5,5	31,5	72,5	34,5	24	48,5	7	50	38	35	M6-20	63	-	45	63
B 14	25	5,5	31,5	72,5	34,5	24	48,5	7	50	38	35	M6-20	45	63	45	63
B 15	25	5,5	31,5	72,5	34,5	24	48,5	7	50	38	35	M6-20	45	63	45	63
B 16	25	5,5	31,5	72,5	34,5	24	48,5	7	50	38	35	M6-20	45	63	45	63
B 18	25	5,5	31,5	72,5	34,5	24	48,5	7	50	38	35	M6-20	45	63	45	63
B 20 *	25	5,5	31,5	72,5	34,5	24	48,5	7	50	38	35	M6-20	45	63	45	63

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish
 - Plain, matte shot-blasted
- Stainless steel AISI CF-8
- Socket cap screws DIN 912
- Hex nuts DIN 985
- Stainless Steel Characteristics
- RoHS

Accessory

- Adjustable Hand Levers GN 911 / GN 911.3

Information

Swivel clamp connector joints GN 281 are an assembly of the swivel clamp connectors GN 271 and GN 275. The clamping bore is mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462. At the screw location z₁, the socket cap screw reduces the bore cross-section for clamping. For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 / GN 911.3 listed in the table as accessory. see also... Construction Tubes GN 990 Retaining Rods / Tubes GN 480.1 Swivel Clamp Connector Bases GN 271 Swivel Clamp Connectors GN 275

How to order (Aluminum)		1	d ₁
		2	Identification no.
		3	Finish
GN281-B14-2-BL			
How to order (Stainless steel)		1	d ₁
		2	Identification no.
		3	Material
GN281-B16-2-NI			