


ROSTFREI
Inox
Stainless
Steel

3 Type
AS With external hex
IS With internal hexalobular



1

2

2

l ₁	d ₁ Thread				d ₂ H7 Bore	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
30	M 3	-	-	-	-	10	13	24,5	4	31	3,5	7
30	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	31	3,5	8
45	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	34	3,5	8
63	M 6	M 8	-	B 8	-	13,5	17,5	31	6,5	45	4	11
78	M 8	M 10	M 12	B 8	B 10	16	21	36	8	54	4	14
92	M 10	M 12	-	B 12	-	19	24	43	11	64	4	17

Specification

- GN 300.5**
Handle
Stainless steel precision casting AISI CF-8
Matte shot-blasted
- GN 300.6**
Handle
Stainless steel precision casting AISI CF-8
Polished
- Bushing
Stainless steel AISI 303
- Retaining screw
Stainless steel AISI 303
- Pressure spring
Stainless steel AISI 301
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

On request

- With inch threads

Information

Adjustable hand levers GN 300.5 / GN 300.6 with solid stainless steel handle, correspond to applications where „aggressive“ surrounding conditions are given, or where stainless steel materials are prescribed such as in food processing or chemical industry.

Retaining screws with hex head (Type AS) comply with the requirement „prevents water from accumulating“.

Adjustable hand levers have proved to be ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

How to order (Matte shot-blasted)

1 l₁
 2 d₁
 3 Type
GN 300.5-78-M10-AS

How to order (Polished)

1 l₁
 2 d₁
 3 Type
GN 300.6-92-M12- IS