



1 2 3

1			2			3						d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	
l ₁	d ₁		l ₂															
30	M 3	-	6	8	10	12	16	-	-	-	10	13	26,5	4	31	3,5		
30	M 4	-	12	16	20	25	32	-	-	-	10	13	26,5	4	31	3,5		
30	M 5	M 6	12	16	20	25	32	40	50	-	10	13	26,5	4	31	3,5		
45	M 4	-	12	16	20	25	32	-	-	-	10	13	26,5	4	35	3,5		
45	M 5	M 6	12	16	20	25	32	40	50	-	10	13	26,5	4	35	3,5		
63	M 6	M 8	12	16	20	25	32	40	50	63	13,5	17,5	32,5	6,5	45	4		
63	M 10	-	20	25	32	40	50	63	-	-	13,5	17,5	32,5	6,5	45	4		
78	M 8	M 10	16	20	25	32	40	50	63	80	16	21	37,5	8	55	4		

Specification

Handle

Zinc die casting
Powder coated
Black, RAL 9005, textured finish

4 5
● SW

Insert

Plastic, Polyamide (PA)
• Black, RAL 9005
• Orange, RAL 2004
• Gray, RAL 7035

● S
● O
● G

Threaded stud

Stainless steel AISI 303

RoHS

On request

• Handle in GN 300 colors

Adjustable hand levers GN 303.1 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be dis-engaged. The releasing button is a design element that offers an easy disengagement. Its use is limited to applications where dismantling of the lever for installation is not required.

see also...

GN 303.2 Adjustable Hand Levers (Insert Steel, with Releasing Button) QVX

Technical Information

Stainless Steel Characteristics

Page

QVX

QVX

How to order

1	l ₁
2	d ₁
3	l ₂
4	Color handle
5	Color releasing button

GN 303.1-63-M8-32-SW-G

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

