


1

Type

D1 With elastomer insert

2

| d <sub>1</sub><br>Nominal dimension |    |    |    |    |    | b <sub>1</sub> | b <sub>2</sub> ±1 | d <sub>2</sub> | Length l ≈ | m ≈ | s <sub>1</sub> ≈ | s <sub>2</sub> ≈ |
|-------------------------------------|----|----|----|----|----|----------------|-------------------|----------------|------------|-----|------------------|------------------|
| 8                                   | 10 | 11 | 12 | 13 | 14 | 15             | 19                | 6,4            | 17,2       | 9,7 | 3,2              | 3,7              |
| 15                                  | 16 | 17 | 18 | 19 | 20 | 15             | 19                | 6,4            | 17,2       | 9,7 | 3,2              | 3,7              |
| 21                                  | 22 | 23 | 24 | 25 | -  | 15             | 19                | 6,4            | 17,2       | 9,7 | 3,2              | 3,7              |
| 26                                  | 27 | 28 | 29 | 30 | -  | 15             | 19                | 6,4            | 17,2       | 9,7 | 3,2              | 3,7              |

3

| b <sub>1</sub> | b <sub>2</sub> ±1 | d <sub>2</sub> | Length l ≈ | m ≈ | s <sub>1</sub> ≈ | s <sub>2</sub> ≈ |
|----------------|-------------------|----------------|------------|-----|------------------|------------------|
| 15             | 19                | 6,4            | 17,2       | 9,7 | 3,2              | 3,7              |
| 15             | 19                | 6,4            | 17,2       | 9,7 | 3,2              | 3,7              |
| 15             | 19                | 6,4            | 17,2       | 9,7 | 3,2              | 3,7              |
| 15             | 19                | 6,4            | 17,2       | 9,7 | 3,2              | 3,7              |

Specification

4

5

Loop clamp

Steel

Zinc plated

W1

Elastomer insert

Ethylene propylene diene rubber (EPDM)

RoHS

E

On request

• Additional clamping ranges

• Other materials

Loop clamps DIN 3016 securely and compactly fasten hoses, cables and cable conduit in machines, plants or vehicles. Reinforcement in the area of the fixing holes increases the stability. The elastomer insert prevents chafing and improves the clamping effect.

see also... [ganternorm.com](https://ganternorm.com)

DIN 3017 Hose Clamps (Steel / Stainless Steel)  
DIN 3017 T-Bolt Hose Clamps (Steel / Stainless Steel)  
GN 3017.5 Spring Clamps (Steel)

Technical Information

Plastic Characteristics

Stainless Steel Characteristics

How to order

1

2

3

4

5

DIN 3016-D1-10-15-W1-E

1 Type

2 d<sub>1</sub>

3 b<sub>1</sub>

4 Material (loop clamp)

5 Material (elastomer insert)