



3 Type

- E Angled lever
- D Straight lever

1

2

d ₁	d ₂	d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄		h ₅	l ₂		l ₃	t	
								Type E	Type D		Type E	Type D			
21	M 6	M 8	13,5	8	20	37	34,5	4,5	62	39	3	75	81	70	11
24	M 8	M 10	16	10	25	44	41	6,5	78	47	3,5	101	108	96	14
28	M 10	M 12	19	12	30	53	49	8,5	93	56	4	116	124	110	17
33	M 12	M 16	23	12	32	60	56	10,5	105	65	4,5	131	140,5	124	22

Specification

- Steel
Blackened
- Ball knobs DIN 319
Plastic, Duroplast
Black, shiny finish
- RoHS

On request

- With inch threads

Information

Safety tension levers GN 312 are used on such applications where a thoughtless or mistaken releasing or re-positioning of the tension lever could lead to an accident.

The lever in its rest position is not connected with the internal spindle and can be rotated unhindered.

The tension lever engages in the serration only after pushing it down, thus allowing clamping or unclamping.

The „freewheel“ position is re-established as soon as the handle is released.

see also...

- Safety Hand Levers GN 604.2 (Plastic) → Page 494

How to order

GN 312-21-M8-E

1	d ₁
2	d ₂
3	Type