



3 Type

A With countersunk holes

| 1 l_1 | | 2 l_2 | | d_1 | For countersunk screws | d_2 | h_1 | $h_2 \approx$ | l_3 | m_1 | m_2 | m_3 | m_4 | s |
|---------|-----------------|---------|-----|-----------|------------------------|-------|-------|---------------|-------|-------|-------|-------|-------|-----|
| Steel | Stainless steel | | | | | | | | | | | | | |
| 85 | - | 70 | 5,5 | M 4 | 6,5 | 12 | 44 | 75 | 65 | 45 | 45 | 10 | 1,25 | |
| 100 | 100 | 80 | 5,5 | M 4 / M 5 | 7,5 | 14 | 52 | 95 | 75 | 52 | 44 | 22,5 | 1,5 | |
| 120 | - | 95 | 5,5 | M 5 | 7,5 | 15 | 54 | 103,5 | 96 | 70 | 55 | 20 | 1,5 | |
| 135 | - | 110 | 6,4 | M 6 | 10 | 15 | 65 | 123 | 105 | 75 | 73 | 22 | 1,75 | |

Specification

| | |
|---------------------------------|-----------|
| Steel | ST |
| Zinc plated, blue passivated | |
| Stainless steel AISI 304 | NI |
| Plain finish | |
| RoHS | |

Folding handles GN 3136 are used for pulling out drawers or lifting boxes and containers. When in use, the swivel handle strikes the sheet metal housing at around 90° and then returns to its rest position by gravity. Due to the simple design, the stamped and bent parts can have larger tolerances. Appropriate compensation measures should therefore be considered in the design.

| see also... | Page |
|-------------------------------------------------------------------------------------------|------|
| GN 425.8 Folding Handles with Recessed Tray (with Locking or Spring-Loaded Return) | QVX |
| GN 425.9 Folding Handles (Stainless Steel, with / without Retaining Spring) | QVX |
| GN 825.1 Folding Handles (Plastic, with Spring-Loaded Return) | QVX |

Technical Information

| | |
|---------------------------------|-----|
| Stainless Steel Characteristics | QVX |
|---------------------------------|-----|

How to order

GN 3136-100-80-A-ST

| | |
|---|----------|
| 1 | l_1 |
| 2 | l_2 |
| 3 | Type |
| 4 | Material |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

