



1

2

| l_1 | d_1 | | | d_2 | d_3 | h_1 | h_2 | h_3 | h_4 Stroke | t min. |
|-------|-------|------|-----|-------|-------|-------|-------|-------|-----------------|-------------|
| 30 | M 4 | M 5 | M 6 | 10 | 13 | 26,5 | 4 | 31 | 3,5 | 9 |
| 45 | M 4 | M 5 | M 6 | 10 | 13 | 26,5 | 4 | 35 | 3,5 | 9 |
| 63 | M 6 | M 8 | - | 13,5 | 17,5 | 32,5 | 6,5 | 45 | 4 | 11 |
| 78 | M 8 | M 10 | - | 16 | 21 | 37,5 | 8 | 55 | 4 | 14 |

Specification

3

4

- Handle
Zinc die casting
- Powder coated
Black, RAL 9005
Textured finish ● SW
- Releasing button
Plastic
Black, RAL 9005 ● S
Orange, RAL 2004 ● O
Gray, RAL 7035 ● G
- Bushing
Steel
Zinc plated, blue passivated
- RoHS

On request

- Handle in colors of GN 300

Information

Adjustable hand levers GN 303.2 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

The releasing button is a design element that offers an easy disengagement. Its use is limited to applications where dismantling of the lever for installation is not required.

see also...

- Adjustable Hand Levers GN 303.1
(with Push Button, Bushing Stainless Steel) → Page 446

How to order

| | |
|---|------------------------|
| 1 | l_1 |
| 2 | d_1 |
| 3 | Color handle |
| 4 | Color releasing button |

GN303.2-78-M10-SW-G