



1			2			3					d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke
30	M 4	-	12	16	20	25	32	-	-	10	13	26,5	4	31	3,5	
30	M 5	M 6	12	16	20	25	32	40	50	10	13	26,5	4	31	3,5	
45	M 4	-	12	16	20	25	32	-	-	10	13	26,5	4	35	3,5	
45	M 5	M 6	12	16	20	25	32	40	50	10	13	26,5	4	35	3,5	
63	M 6	M 8	16	20	25	32	40	50	63	13,5	17,5	32,5	6,5	45	4	
78	M 8	M 10	20	25	32	40	50	63	80	16	21	37,5	8	55	4	

Specification

- Handle
Zinc die casting
- Powder coated
Black, RAL 9005
Textured finish ● SW
- Releasing button
Plastic
Black, RAL 9005 ● S
Orange, RAL 2004 ● O
Gray, RAL 7035 ● G
- Threaded stud
Steel
Zinc plated, blue passivated
- RoHS

On request

- Handle in colors of GN 300

Information

Adjustable hand levers GN 303.2 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

The releasing button is a design element that offers an easy disengagement. Its use is limited to applications where dismantling of the lever for installation is not required.

see also...

- Adjustable Hand Levers GN 303.1
(with Push Button, Threaded Stud Stainless Steel) → Page 447

How to order		1	l ₁
		2	d ₁
		3	l ₂
		4	Color handle
		5	Color releasing button

1 2 3 4 5
GN 303.2-63-M8-25-SW-G