



d₁ Ø Insert	d₂ Thread	d₃ H7 Bore with Keyway	s₁ Square	s₂ Hexagon	b	d₄	d₅	h	Length l	max. torque in Nm
12	M 8	-	V 8	-	22	9	20	11	118	40
17	M 10	M 12	V 10	SK 12	30	11	26	14	156	70
22	M 14	M 16	V 12	V 14	39,5	14	33	17	187	130
26	M 20	-	V 17	SK 17	46	17	33	22	219	180

Specification

- Housing
Steel
Powder coated
Black matte, textured finish
- Shaft
Stainless steel AISI 303
Matte shot-blasted
- Wearing parts
Steel, hardened
- Domes gear knobs GN 719.1
Plastic, Duroplast
Black, shiny finish
- Keyway P9 DIN 6885 Page 1 → Page 2078
- Squares DIN 79 → Page 2082
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

On request

- Other inserts

Information

Ratchet spanners GN 316 are robust, easy to handle and have an appropriate and attractive design.

Ratchet spanners are normally used wherever the same ratchet insert is always required or where it makes sense to leave the ratchet spanner at the place of use or attach it to equipment or machinery as a „stationary“ tool. Various different versions of ratchet insert are available and these can be exchanged as required by loosening the retaining screw and removing the cover plate.

The ratchet action is deactivated when the reversing lever is in the locked position (central position), allowing torque to be applied in both directions.

see also...

- Countersunk Washers GN 184 (for Axial Fixing) → Page 1090
- Domed Gear Knobs GN 719.1 → Page 61

How to order	1 d ₁
	2 s ₁ (s ₂ , d ₂ , d ₃)

GN316-26-V17