



- 4 Type**
- MS** Brass tip
  - KU** Plastic tip
  - DZ** Hardened oval tip
  - ZK** Spherical end
  - KD** Spherical end with thrust pad

	1	2	3																				
	$l_1$	$d_1$	$l_2$	$d_3$	$d_4$	$d_5$	$d_6$	$d_7 + 0,05$	$d_8$	$h_1$	$h_2$	$h_3$	$h_4$ Stroke	$l_3$	$l_4$	$l_5$	$l_6$	$l_7$					
	30	M 6	16	20	25	32	40	50	10	13	4	3,5	4,5	15	24,5	4	31	3,5	1	1,3	1,8	5,1	3,6
	45	M 6	16	20	25	32	40	50	10	13	4	3,5	4,5	15	24,5	4	35	3,5	1	1,3	1,8	5,1	3,6
	63	M 8	20	25	32	40	50	63	13,5	17,5	6	5	6,1	18	31	6,5	45	4	1,5	1,6	2,5	6,2	4,2
	63	M 10	20	25	32	40	50	63	13,5	17,5	8	6,5	7,8	21	31	6,5	45	4	2	1,9	3,5	7,3	4,3

**Specification**

- Handle
  - Zinc die casting
  - Powder coated
  - Black, RAL 9005, textured finish ● **SW**
  - Orange, RAL 2004, textured finish ● **OS**
  - Red, RAL 3000, textured finish ● **RS**
  - Silver, RAL 9006, textured finish ● **SR**
- Threaded stud and retaining screw  
Steel (5.8), blackened
- Thrust point
  - Type MS: Brass
  - Type KU: Plastic (POM)
  - Type DZ: Steel, hardened (oval point)
- Thrust pad  
Plastic (Polyacetal POM)
  - Temperature resistant up to 80 °C
  - Black, matte finish
- *Strength Values of Screws* → Page 2152
- RoHS

**On request**

- With threaded stud in stainless steel
- Flat handle (GN 302)

**5 Information**

Adjustable hand levers GN 306 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged. Pulling the lever disengages the serrations, allowing it to be swivelled to the ideal clamping position. When the lever is released, the serrations automatically re-engage.

The brass and plastic tipped studs (Types MS / KU) help to avoid damage to the work piece being clamped.

The hardened tipped stud (Type DZ) provides an oval point-shaped pressure point.

The swivel thrust pad (Type KD) can easily be snapped on and taken off. Pad is supplied unmounted.

see also...

- *Adjustable Hand Levers GN 300 (without Special Tipped Threaded Stud)*  
→ Page 428 / 429

How to order		1	$l_1$
		2	$d_1$
		3	$l_2$
		4	Type
		5	Color

**GN 306-45-M6-20-DZ-OS**