



3 Type

- A** With threaded stud
- B** With internal thread

| 1 d_1 | 2 d_2 | d_3 | l_1 | $l_2 \pm 1$ | $l_3 \pm 1$ | A/F | t min. |
|----------------|----------------|-------|-------|-------------|-------------|-----|--------|
| 25 | M 6 | 10 | 11 | 37,5 | 15 | 8 | 10 |
| 32 | M 8 | 13 | 13 | 48 | 19 | 10 | 12 |
| 40 | M 10 | 16 | 14 | 61 | 24 | 14 | 16 |
| 50 | M 12 | 20 | 21 | 78 | 31 | 17 | 16 |

Specification

Knob

- Plastic, phenolic resin (PF)
- Operating temperature up to 110 °C
- Black, shiny finish

GN 319.2

Spindle

- Steel
- Zinc plated, blue passivated

GN 319.5

Spindle

- Stainless steel AISI 303
- Matte shot-blasted

RoHS

Revolving ball knobs GN 319.2 / GN 319.5 are in general used where a pulling action is involved such as on vertically positioned handwheels.

see also...

GN 597.1 Revolving Mushroom Shaped Handles

Page

QVX

Technical Information

Plastic Characteristics

QVX

Stainless Steel Characteristics

QVX

How to order (Spindle steel)

GN 319.2-32-M8-A

- 1** d_1
- 2** d_2
- 3** Type

How to order (Spindle stainless steel)

GN 319.5-32-M8-B

- 1** d_1
- 2** d_2
- 3** Type

