



- 3 Type
- A

Mounting from the back (threaded blind bore)
- B

Mounting from the operator's side (only for d₁=28)

d ₁	Length l ±0,25							d ₂	b ₁	b ₂	b ₃	b ₄	h ₁	h ₂	t min.
	180	200	250	300	350	400	-								
20	180	200	250	300	350	400	-	M 6	24	12	42	54	42	54	12
28	200	250	300	350	400	500	600	M 8	25	14	50	66	50	66	15
30	200	300	350	400	500	600	1000	M 8	27	17	51	68	51	68	15

Specification

- 1

2
- 4
- 1

Handle tube
Aluminum (wall thickness 1,5)
- 2

Handle legs
Zinc die casting
- 3

Tube
Powder coated
Black, RAL 9005, textured finish
Handle legs powder coated
Black, RAL 9005, textured finish
- 4

Tube, anodized, natural color
Handle legs powder coated
Black, RAL 9005, textured finish
- 5

Tube, anodized, natural color
Handle legs powder coated
Silver, RAL 9006, textured finish
- 6

Cover
Plastic, light gray
- 7

Cover cap (Type B)
Plastic (Technopolymer)
- Black (for SW / EL)
- Light gray (for ES)
- 8

Load Rating Information → Page 2106
- 9

RoHS

Accessory

- 1

Handle legs GN 333.8 → Page 183

Information

The handle tube of the GN 333 tubular handles can be screwed to the handle bases without further machining or processing, allowing **special lengths** to be realised easily.

A typical application area for tubular handles GN 333 are double-winged doors at machines or devices.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles Ø 28 (Type A) are available under GN 333.8.

see also...

1

Product Family Standard Parts for Profile Systems → Page 18

2

Tubular Handles GN 333.1 (Straight) → Page 180

3

Tubular Handles GN 332 (with Power Switching Function) → Page 190

4

Assembly Sets for Profile Systems 30 / 40 GN 965 → Page 2086

5

Assembly Sets for Profile Systems 30 / 40 / 45 GN 968 → Page 2096

How to order		1	d ₁
		2	Length l
		3	Type
		4	Finish
GN 333-28-600-A-EL			