



3 Type

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side (only for $d_1 = 28$)

1 2

d_1	l_1						d_2	d_3	b_1	b_2	h_1	h_2	h_3	l_2 max.	l_3	t min.
20	180	200	250	300	350	400	-	M 6	-	24	12	42	54	-	-	12
28	200	250	300	350	400	500	600	M 8	M 6	25	14	50	66	7	6	13
30	200	300	350	400	500	600	1000	M 8	-	27	17	51	68	-	-	15

4 Specification

Handle tube

Aluminum, wall thickness 1,5 mm

- Powder coated
Black, RAL 9005, textured finish
- Anodized, natural color
- Anodized, natural color

- **SW**
- **EL**
- **ES**

Handle legs

- Zinc die casting
- Powder coated, textured finish
- Black, RAL 9005 for SW / EL
- Silver, RAL 9006 for ES

Cover

Plastic, light gray

Fastening set for type B

- Socket button head screws ISO 7380-M6-20
Steel, zinc plated
- Black passivated for SW / EL
- Blue passivated for ES
- Hex nuts ISO 4032-M6
Steel, zinc plated, blue passivated
- Washers DIN 125
Steel, zinc plated, blue passivated

RoHS

The handle tube of the GN 333.1 tubular handles can be screwed to the handle bases without further machining or processing, allowing **special lengths** to be realised easily.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles $\varnothing 28$ (type A) are available under GN 333.9.

For type B, socket button head screws, hex nuts and washers are included parts of the order.

see also...

	Page
GN 333 Tubular Handles (Angled)	QVX
GN 333.7 Tubular Handles (Stainless Steel)	QVX
GN 331 Tubular Handles (with Electrical Switching Function)	QVX

Technical Information

Load Rating Information	QVX
-------------------------	-----

Accessory

GN 333.9 Handle Legs (for Tubes $\varnothing 28$, Angled)	QVX
--	-----

How to order

1	d_1
2	l_1
3	Type
4	Finish

GN 333.1-28-400-B-SW