



d_0 = Shaft collar $\varnothing d_1$	l_1	d_1	h_2	d_2	d_3	l_2	h_1	h_3
16	22	M 3	7	5,7	10,5	8	24	22
20 / 22	22	M 3	8	5,7	10,5	10	24	22
26	22	M 4	9	7,2	10,5	10	26	24
30 / 32	30	M 4	12	7,2	13	12	32	30
36	30	M 5	13	8,7	13	12	33,5	31
42	30	M 5	15	8,7	13	14	35	33
48	45	M 5	16	8,7	13	16	36,5	34
55	45	M 6	18	10	13	16	38,5	36
60	45	M 6	19	10	13	16	39,5	37
65	45	M 6	20	10	13	18	40,5	38

Specification

Handle

Zinc die casting
Powder coated
Black, RAL 9005, textured finish

● SW

Insert

Stainless steel AISI 303

Retaining screw

Stainless steel AISI 304

RoHS

For shaft collars of the standard families GN 706... and GN 707..., adjustable hand levers GN 311 replace the hex socket screw DIN 912. That allows the shaft collars to be adjusted easily and quickly without tools.

The table of dimensions of the shaft collars shows the corresponding hand lever for the respective shaft collar size d_1 .

Semi-split shaft collars GN 706.2 including hand lever are available under GN 706.4.

see also...

	Page
GN 706.2 Semi-Split Shaft Collars	QVX
GN 707.2 Split Shaft Collars	QVX
GN 706.4 Semi-Split Shaft Collars (with Hand Lever)	QVX

Technical Information

Stainless Steel Characteristics

QVX

How to order



1	l_1
2	d_1
3	h_2
4	Color