


- 3 Type**
- A Mounting from the back (threaded blind bore)
 - B Mounting from the operator's side



1		2																
b ₁	l ₁ ±0,5					a	b ₂	b ₃	d	h ₁	h ₂	h ₃	l ₂ max.	l ₃	t min.			
36	200	250	300	350	400	500	600	800	24	22	38	M 8	60,5	79,5	5	16,5	25	15

Specification 4

- Handle tube**
 Aluminum
- Powder coated
 Black, RAL 9005, textured finish ● SW
 - Anodized, natural color
 Handle legs black ● EL
 - Anodized, natural color
 Handle legs silver ● ES

- Handle legs**
 Zinc die casting
 Powder coated, textured finish
- Black, RAL 9005 for SW / EL
 - Silver, RAL 9006 for ES

Cover
 Plastic, light gray

- Fastening set for type B**
 Stainless steel
- Socket button head screws ISO 7380-M8-30
 - Hex nuts ISO 4032
 - Washers DIN 125

RoHS

Oval tubular handles GN 335 have an inclined handle profile with a 45° angle. These handles are comfortable and ergonomic to grasp in a variety of applications such as sliding doors.

For type B, socket button head screws, hex nuts and washers are included parts of the order.

The tubular handle can be screwed onto the handle shanks without further modification. This allows even a small quantity of special lengths to be ordered.

see also...	Page
GN 334 Oval Tubular Handles (Mounting from the Back)	QVX
GN 334.1 Oval Tubular Handles (Mounting from the Operator's Side)	QVX

Technical Information	
Load Rating Information	QVX

How to order	
1	b ₁
2	l ₁
3	Type
4	Finish

GN 335-36-500-A-SW