



- 3 Type**
- A** Mounting from the back (threaded blind bore)
 - B** Mounting from the operators side

Socket button head screw ISO 7380
 Washer DIN 125
 Hex nut ISO 4032
 Stainless Steel AISI 304

1 2

b_1	$l_1 \pm 0,5$	a	b_2	b_3	d	h_1	h_2	h_3	l_2 max.	l_3	t min.
36	200 250 300 350 400 500 600 800	24	22	38	M 8	60,5	79,5	5	16,5	25	15

Specification

- Handle tube
Aluminum
- Handle legs
Zinc die casting
Powder coated
- Tube ● **SW**
Black, RAL 9005, textured finish
Powder coated
Handle legs
Black, RAL 9005, textured finish
- Tube ● **EL**
Anodized, natural color
Handle legs
Black, RAL 9005, textured finish
- Tube ● **ES**
Anodized, natural color
Handle legs
Silver, RAL 9006, textured finish
- Cover
Plastic, light gray
- *Load Rating Information* → Page 2106
- **RoHS**

Information

Oval tubular handles GN 335 have an inclined handle profile with a 45° angle. These handles are comfortable and ergonomic to grasp in a variety of applications such as sliding doors.

For type B, socket button head screws, hexagon nuts and washers are included parts of the order.

The tubular handle can be screwed onto the handle shanks without further modification. This allows even a small quantity of **special lengths** to be ordered.

see also...

- *Oval Tubular Handles GN 334 (Mounting from the Back)* → Page 196
- *Oval Tubular Handles GN 334.1 (Mounting from the Operators Side)* → Page 197
- *Assembly Sets for Profile Systems 30 / 40 GN 965* → Page 2086
- *Assembly Sets for Profile Systems 30 / 40 / 45 GN 968* → Page 2096

How to order	1 b
1 2 3 4	2 l_1
GN 335-36-500-A-SW	3 Type
	4 Finish