



4 Type
E Angled lever
D Straight lever

1 2 3

d ₁	d ₂	l ₁		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄		h ₅	l ₂		l ₃					
		Type E	Type D							Stroke	Type E		Type D							
21	M 8	16	20	25	32	40	50	63	13,5	8	20	37	34,5	4,5	62	39	3	75	81	70
24	M 10	20	25	32	40	50	63	80	16	10	25	44	41	6,5	78	47	3,5	101	108	96
28	M 12	20	25	32	40	50	63	80	19	12	30	53	49	8,5	93	56	4	116	124	110
33	M 16	32	40	50	63	80	-	-	23	12	32	60	56	10,5	105	65	4,5	131	140,5	124

Specification

- Steel
 Blackened
 Threaded stud
 Property class 5.8
- Ball knobs DIN 319
 Plastic, Duroplast
 Black, shiny finish
- *Strength Values of Screws* → Page 2152
- RoHS

On request

- With inch threads

Information

Safety tension levers GN 312 are used on such applications where a thoughtless or mistaken releasing or re-positioning of the tension lever could lead to an accident.

The lever in its rest position is not connected with the internal spindle and can be rotated unhindered.

The tension lever engages in the serration only after pushing it down, thus allowing clamping or unclamping.

The „freewheel“ position is re-established as soon as the handle is released.

see also...

- *Safety Hand Levers GN 604.2 (Plastic)* → Page 495

How to order

GN312-24-M10-32-E

- 1 d₁
- 2 d₂
- 3 l₁
- 4 Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

