



elesa

Original design S.N

 Type

B With polyamide bushing

1

2

d_1	d_2	t	$d_3 \approx$	$h \approx$
20	B 6	13	7	19
25	B 6	14	10	24
25	B 8	14	10	24
30	B 8	14	15	28
30	B 10	18	15	28
35	B 8	14	15	33
35	B 10	18	15	33
40	B 10	18	15	38
40	B 12	21	15	38
45	B 12	21	21	42,5
45	B 14	24	21	42,5
50	B 12	21	21	47,5
50	B 14	24	21	47,5
50	B 16	28	21	47,5

Specification

Plastic, phenolic resin (PF)

- Operating temperature up to 110 °C
- Black, shiny finish
- Bushing polyamide, embedded

RoHS

The ball knobs GN 319.1 do not require a thread at the shaft.

During mounting, easy blows with a soft hammer are sufficient to drive the knob into place; the shaft end should be slightly rounded or chamfered (30°). The bore is conical which guarantees a firm press on operation.

The elastical polyamide bushing shows a good holding force even with a shaft tolerance of h11, the knobs are resistant to vibrations and may be re-assembled any time.

see also...

GN 719.1 Domed Gear Knobs (Press-On Type)

Page

QVX

Technical Information

ISO Fundamental Tolerances

QVX

Plastic Characteristics

QVX

How to order

GN 319.1-40-B10-B

1	d_1
2	d_2
3	Type