



3 Type

- A** With threaded stud
- B** With internal thread

1 d_1	2 d_2	d_3	l_1	$l_2 \pm 1$	$l_3 \pm 1$	A/F	t min.
25	M 6	10	11	37,5	15	8	10
32	M 8	13	13	48	19	10	12
40	M 10	16	14	61	24	14	16
50	M 12	20	21	78	31	17	16

Specification

Knob

- Plastic, phenolic resin (PF)
- Operating temperature up to 110 °C
- Black, shiny finish

GN 319.2

Spindle

- Steel
- Zinc plated, blue passivated

GN 319.5

Spindle

- Stainless steel AISI 303
- Matte shot-blasted

RoHS

On request

With inch threads

Revolving ball knobs GN 319.2 / GN 319.5 are in general used where a pulling action is involved such as on vertically positioned handwheels.

see also...

	Page
GN 597.1 Revolving Mushroom Shaped Handles	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Spindle steel)

GN 319.2-32-M8-A

1	d_1
2	d_2
3	Type

How to order (Spindle stainless steel)

GN 319.5-32-M8-B

1	d_1
2	d_2
3	Type

