



4 Type

- A** Without nut, without rubber pad
- B** With nut, without rubber pad
- AG** Without nut, with rubber pad
- BG** With nut, with rubber pad

1 2 3

d ₁	d ₂	l ₁			l ₂		l ₃		A/F	Ball Ø	Static load in kN (see information)
60	M 8	43	68	-	-	33	24	14	14	14	
60	M 10	43	68	98	-	33	24	14	14	14	
60	M 12	43	68	98	-	33	24	14	14	14	
60	M 14	68	98	148	-	33	24	14	14	14	
60	M 16	68	108	148	168	33	24	16	14	14	
60	M 16	58	98	138	158	43	24	24	24	18	
60	M 20	98	138	158	198	43	24	24	24	18	
60	M 24	98	138	158	198	43	24	24	24	18	
80	M 8	43	68	-	-	33	24	14	14	14	
80	M 10	43	68	98	-	33	24	14	14	16	
80	M 12	43	68	98	-	33	24	14	14	16	
80	M 14	68	98	148	-	33	24	14	14	16	
80	M 16	68	108	148	168	33	24	16	14	16	
80	M 16	58	98	138	158	43	24	24	24	18	
80	M 20	98	138	158	198	43	24	24	24	18	
80	M 24	98	138	158	198	43	24	24	24	18	
100	M 8	43	68	-	-	33	24	14	14	18	
100	M 10	43	68	98	-	33	24	14	14	18	
100	M 12	43	68	98	-	33	24	14	14	18	
100	M 14	68	98	148	-	33	24	14	14	18	
100	M 16	68	108	148	168	33	24	16	14	18	
100	M 16	58	98	138	158	43	24	24	24	25	
100	M 20	98	138	158	198	43	24	24	24	25	
100	M 24	98	138	158	198	43	24	24	24	25	
125	M 16	58	98	138	158	67	46	24	24	28	
125	M 20	98	138	158	198	67	46	24	24	28	
125	M 24	98	138	158	198	67	46	24	24	28	



3.1

3.2

3.3

3.4

3.5

Specification

- Foot
Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Black, matte finish
 - Temperature resistant up to 100 °C
- Rubber pad (NBR)
70 Shore A, black
- **GN 344**
 - Threaded stud steel
Property class 5.8
Zinc plated, blue passivated
 - Hexagon nut ISO 4032
Steel zinc plated, blue passivated
- **GN 344.5**
 - Threaded stud
Stainless steel AISI 303
 - Hexagon nut ISO 4032
Stainless steel AISI 304
- *Strength Values* → Page 2152
- *Elastomer Characteristics* → Page 2158
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Leveling feet GN 344 / GN 344.5 are capable of withstanding high static loads through the use of a high density plastic material coupled with a design which distributes the load over a larger area.

The values given in the table regarding the static load capacity serve as a guide line only and if these are exceeded serious permanent deformation or breakage of the plastic socket could occur.

The values were arrived at by a series of tests whereby a limited number of leveling feet were subjected for a limited time to a vertical static load to the feet.

The details relating to the static load are non-binding recommended values and rule out any liability. They constitute no general warranty of quality and condition. The user must determine from case to case whether a product is suitable for the intended use.

Leveling feet GN 344 / GN 344.5 are supplied assembled, but are removable.

3.6

3.7

3.8

3.9

How to order (Threaded stud steel)

GN 344-80-M16-138-BG

1	d ₁
2	d ₂
3	l ₁
4	Type

How to order (Threaded stud stainless steel)

GN 344.5-100-M20-158-A

1	d ₁
2	d ₂
3	l ₁
4	Type

