



4 Type

- C** With tapped hole, without bushing
- E** With tapped bushing

d ₁	2 3				3				d ₄ ≈	h ≈	t ₁ min.	t ₂ min.	
	KU Type C Thread		KT Type C Thread		KU Type E Thread		KT Type E Thread						
10	M 3	-	-	-	-	-	-	-	5	9,3	5	-	
12	M 4	-	-	-	-	-	-	-	6	11,2	6	-	
16	M 4	M 5	-	M 4	M 5	M 4**	-	M 4	M 5	8	15	6	6
20	M 5	M 6	-	M 5	M 6	M 5	-	M 5	M 6	12	18	7,5	7,5
25	M 5	M 6	M 8	M 6	M 8	M 6	M 8*	M 6	M 8	15	22,5	9	9
30	M 6	M 8	-	-	-	-	-	-	-	15	28	12	-
32	M 6	M 8	M 10	M 8	M 10	M 8	-	M 8	M 10	18	29	12	12
35	M 8	M 10	-	-	-	-	-	-	-	18	32,5	15	-
40	M 8	M 10	M 12	M 10	M 12	M 10	M 12*	M 10	M 12	22	37	15	15
50	M 10	M 12	-	-	-	M 12	-	-	-	28	46	18	18

* This size is only available in black with bushing in steel. ** This size is only available in black with bushing in brass.

Specification

Plastic , Phenolic resin (PF)	KU
• Flash removed and polished finish	
• Black	● —
• Red, similar RAL 3003	● RT
• Bushing (Type E)	
- Steel, zinc plated	—
- Brass (only in black)	MS
Plastic , Polyamide (PA)	KT
• Shock resistant	
• Black, matt	● —
• Red, similar RAL 3003	● RT
• Bushing (Type E)	
Steel, zinc plated	

RoHS

Technical Information	Page
Plastic Characteristics	QVX

Ball knobs DIN 319 in sizes 30 and 35, as well as various thread of type C and ball knobs made of technopolymer (KT) are not on the official DIN standard sheet.

see also...

DIN 319 Ball Knobs (Press-On Type)	Page
GN 319.1 Ball Knobs (Press-On Type)	QVX
DIN 319 Ball Knobs (Steel, Stainless Steel, Aluminium)	QVX

How to order (Black, without bushing)

1	Material
2	d ₁
3	d ₂
4	Type

1 2 3 4

DIN 319-KU-25-M6-C

How to order (Red, with bushing steel)

1	Material
2	d ₁
3	d ₃
4	Type
5	Color

1 2 3 4 5

DIN 319-KT-32-M8-E-RT

How to order (Black, with bushing brass)

1	Material
2	d ₁
3	d ₃
4	Type
5	Bushing

1 2 3 4 5

DIN 319-KU-25-M6-E-MS