



3 Type

- A Without handle
- D With revolving handle

1 2

d ₁	d ₂ H7 Bore with keyway			d ₃	d ₄	d ₅	d ₆ max.	b	h	l ₁	l ₂	l ₃	r	Ø Handle
140	K 12	K 14	K 16	24	42	40	23	16,5	7	45	58	67,5	61	23
160	K 12	K 14	K 16	24	42	40	23	18	7	45	58	82,5	71	26

Specification

- Handwheel body
Aluminum
 - Rim turned and polished
 - Unmachined surface
Powder coated
Black, textured finish
- Coupling attachments
 - Steel, hardened
 - Glide surfaces honed
- Cover cap
Plastic, light gray
- Revolving handles GN 598
 - Steel, powder coated
Black, textured finish
 - Spindle steel
Zinc plated, blue passivated
- Keyway P9 DIN 6885 Page 2 → Page 2079
- ISO Fundamental Tolerances → Page 2151
- RoHS

Information

The cover cap protects the bearing from dust and dirt while covering fastening elements such as countersunk washers GN 184.

For fastening of the cover cap, the handwheel possesses a groove that is gripped by the elastic segments of the cap.

The cover cap is pressed on by hand and can be pried out with a screwdriver at the indented point.

The needle bearings are greased during assembly, providing ample permanent lubrication.

see also...

- More Information to Safety Handwheels → Page 268
- Countersunk Washers GN 184 (for Axial Fixing) → Page 1090

How to order

GN 321.6-160-K14-D

1	d ₁
2	d ₂
3	Type

Details hub with coupling attachments

