



- 4 Type**
- A** Without nut, without rubber underlay
 - B** With nut, without rubber underlay
 - AG** Without nut, with rubber underlay
 - BG** With nut, with rubber underlay

1 2 3

d ₁	d ₂	l ₁				l ₂	l ₃	l ₄	d ₃	k	A/F	Ball Ø	Static load in kN (see information)
80	M 8	43	68	-	-	33	23	24	8,5	54	14	14	16
80	M 10	43	68	98	-	33	23	24	8,5	54	14	14	16
80	M 12	43	68	98	-	33	23	24	8,5	54	14	14	16
80	M 14	68	98	148	-	33	23	24	8,5	54	14	14	16
80	M 16	68	108	148	168	33	23	24	8,5	54	16	14	16
80	M 16	58	98	138	158	43	23	24	8,5	54	24	24	18
80	M 20	98	138	158	198	43	23	24	8,5	54	24	24	18
80	M 24	98	138	158	198	43	23	24	8,5	54	24	24	18
100	M 8	43	68	-	-	33	23	24	12,5	70	14	14	18
100	M 10	43	68	98	-	33	23	24	12,5	70	14	14	18
100	M 12	43	68	98	-	33	23	24	12,5	70	14	14	18
100	M 14	68	98	148	-	33	23	24	12,5	70	14	14	18
100	M 16	68	108	148	168	33	23	24	12,5	70	16	14	18
100	M 16	58	98	138	158	43	23	24	12,5	70	24	24	25
100	M 20	98	138	158	198	43	23	24	12,5	70	24	24	25
100	M 24	98	138	158	198	43	23	24	12,5	70	24	24	25
125	M 20	98	138	158	198	67	23	46	12,5	95	24	24	28
125	M 16	58	98	138	158	67	23	46	12,5	95	24	24	28
125	M 24	98	138	158	198	67	23	46	12,5	95	24	24	28



3.1

3.2

3.3

3.4

3.5

Specification

- Foot
Plastic Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Black, matte finish
- Temperature resistant up to 100 °C
- Rubber underlay (NBR)
70 Shore A, black
- **GN 345**
- Threaded stud steel
Property class 5.8
Zinc plated, blue passivated
- Hex nut ISO 4032
Steel zinc plated, blue passivated
- **GN 345.5**
- Threaded stud
Stainless steel AISI 303
- Hex nut ISO 4032
Stainless steel AISI 304
- *Strength Values* → Page 2152
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Leveling feet GN 345 / GN 345.5 are capable of withstanding high static loads through the use of a high density plastic material coupled with a design which distributes the load over a larger area.

The values given in the table regarding the static load capacity serve as a guide line only and if these are exceeded serious permanent deformation or breakage of the plastic socket could occur.

The above values have been arrived at by a series of tests whereby a limited number of leveling feet were subjected for a limited time to a vertical static load to the feet.

The fixing holes are closed by a thin plastic layer, which may be easily punctured.

Leveling feet GN 345 / GN 345.5 are supplied assembled, but are removable.

3.6

3.7

3.8

3.9

How to order (Threaded stud steel)	
1	d ₁
2	d ₂
3	l ₁
4	Type
GN 345-100-M20-98-B	

How to order (Threaded stud stainless steel)	
1	d ₁
2	d ₂
3	l ₁
4	Type
GN 345.5-125-M24-158-A	