



Internationaler Designpreis Baden-Württemberg

**2 Bore code**

- B Without keyway
- K With keyway

**4 Type**

- A Without handle
- R With revolving handle

**1**

**3**

d <sub>1</sub>	d <sub>2</sub> H7 Bore		d <sub>3</sub>	b	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	r	Ø Handle GN 798
125	12	14	31	15	18	33	61,5	54	22
140	14	16	36	16,5	19	36	76,5	61	24
160	14	16	36	18	20	39	76,5	71	24
200	18	20	42	20,5	24	45	86,5	89	25
250	22	26	48	23	28	51	86,5	113	25

**Specification**

- Aluminum
  - Hub machined
  - Rim turned on all sides
- Radial and axial runout of the rim < 0.4
- **GN 322**
  - Rim high-polished
  - Unmachined wheel body shot-blasted
- **GN 324**
  - Wheel body completely powder coated
  - Black, textured finish
- Revolving handles GN 798
  - Plastic, Technopolymer
  - Black, matte finish
  - Spindle steel
  - Zinc plated, blue passivated
- *Keyway P9 DIN 6885 Page 1 → Page 2078*
- *Cross Holes GN 110 → Page 2080*
- *ISO Fundamental Tolerances → Page 2151*
- RoHS

**Information**

see also...

- *Safety Handwheels (Disengage the Clutch) → Page 270*
- *Countersunk Washers GN 184 (for Axial Fixing) → Page 1090*
- *Spoked Handwheels GN 924 (Aluminum, Powder Coated) → Page 238*

How to order (Rim polished)

**GN 322 - 140 - K14 - R**

1	d <sub>1</sub>
2	Bore code
3	d <sub>2</sub>
4	Type

How to order (Powder coated)

**GN 324 - 200 - B20 - A**

1	d <sub>1</sub>
2	Bore code
3	d <sub>2</sub>
4	Type