



2 Type

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side

1

$l_1 \pm 0,25$	a	b	d_1 Type A	d_2 Type B	h_1	h_2	l_2	t
120	14	22	M 6	6,5	44	5	141,2	13
140	18	28	M 8	8,5	55	6	166,5	17

Specification

- **GN 328**
Aluminum die casting
- Powder coated
Black, RAL 9005, textured finish ● **SW**
Silver, RAL 9006, textured finish ○ **SR**
- Plain, tumbled ○ **BL**
- **GN 328.5**
Stainless steel
Precision casting AISI 316
Matte shot-blasted **GS**
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

On request

- Other finishes

3

Information

Cabinet U-handles GN 328 / GN 328.5 have excellent stability and ergonomic design. The finger recesses on the underside of the handle provide a specially comfortable grip.

In particular in combination with the larger cabinet U-handle GN 428, they meet the requirements of modern industrial design.

see also...

- *Cabinet U-Handles GN 565* → Page 106
- *Cabinet U-Handles GN 428* → Page 163

How to order (Aluminum)

GN 328-120-A-SW

- 1 l_1
- 2 Type
- 3 Finish

How to order (Stainless steel)

GN 328.5-120-A-GS

- 1 l_1
- 2 Type
- 3 Finish