



3 Type

- A Without slot
- N With slot

Length l ≈	d ₁ H9 Bore	d ₂	h ₁	h ₂ ≈	h ₃ ≈	h ₄ ≈	t +0.5	Ø Handle	Socket cap screw DIN 912
63	B 10	18	28	18	74	40	18	18	M 5
80	B 10	18	28	18	74	40	18	18	M 5
100	B 12	20	30	20	88	50	20	21	M 6
125	B 12	20	30	20	88	50	20	21	M 6

Specification

- Stainless steel AISI 304
 - Shot-blasted
 - Crank butt-welded
- Cover cap
 - Plastic, black
- Revolving handle
 - Plastic, Duroplast
 - Black, shiny finish
 - Temperature resistant up to 110 °C
- Cross Holes GN 110 → Page 2080
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Stainless steel cranked handles GN 369.5 feature a compact design and are used for light drive and positioning tasks. Thanks to the material used, the cranked handles are also suitable for more aggressive environments.

The slot of type N easily transfers the rotary movement to the shaft by means of a transverse pin mounted in the shaft. The cranked handles can be connected removably or permanently fastened axially with a socket cap screw DIN 912. Type A can be ordered with transverse holes for GN 110.

Thanks to a simple manufacturing process, it is relatively easy and inexpensive to produce these cranked handles as special designs.

see also...

- Cranked Handles GN 670.2 (Plastic) → Page 296
- Cranked Handles GN 471 (Aluminum) → Page 286

How to order

GN369.5-125-B12-A

- 1 Length l
- 2 d₁
- 3 Type