



- 3 Type**
- D With plain shaft
  - E With threaded stud

2

d <sub>1</sub>	d <sub>2</sub> h8 Type D ST	d <sub>3</sub> Type E ST			d <sub>4</sub> h13	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub>	A/F Internal hexagon ST / KT
		A4	KT						
16	7	M 6	M 6	-	10	50	11	7	3
20	8	M 8	M 8	M 8	13	64	13	8	4
25	10	M 10	M 10	M 10	16	80	14	10	5
32	13	M 12	-	M 12	20	100	21	13	6
36	16	M 16	-	-	22	112	26	14	8

**Specification**

<b>Steel</b>	<b>ST</b>
Zinc plated, blue passivated	
<b>Steel AISI 316L</b>	<b>A4</b>
<b>Plastic, Polyamide (PA)</b>	<b>KT</b>
<ul style="list-style-type: none"> <li>• Operating temperature up to 100 °C</li> <li>• Black, matte finish</li> <li>• Threaded stud</li> </ul>	
Steel, blackened	

RoHS

On the official DIN standard sheet you can find the additional sizes 10 and 13. For reasons of hygiene, no internal hexagon is used in type A4.

**Technical Information**

	Page
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

**DIN 39-ST-25-E**

1	Material
2	d <sub>1</sub>
3	Type

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

